Rittal – The System.

Faster – better – everywhere.





TS 8601.060

Base/plinth trim panels, side, 100 mm

State: 10/26/2025 (Source: rittal.com/us-en)



TS 8601.060 - Base/plinth trim panels, side, 100 mm for base/plinth components, front and rear

To mount between the base/plinth components. For height 200 mm two 100 mm base/plinth trim panels can be used. Base/Plinth panels can be installed turned at 90° to provide stabilization for bayed base/plinth components.

Features

TS 8601.060
To mount between the base/plinth components. For height 200 mm, two 100 mm base/plinth trim panels can be used.
Carbon steel
Spray-finished
RAL 7022
2 plinth/base trim panels Assembly components
100 mm side trim panels can be installed rotated through 90° to provide stabilization for bayed base/plinth components. Base/plinth baying brackets are required here
Height: 100 mm Height: 3.94 ″

© Rittal 2025 2

Features

Suitable for	Enclosure type: TS: = 600 mm
	Enclosure type: SE
	Enclosure type: CM
	Enclosure type: TP
	Enclosure type: PC
	Enclosure type: IW
	Enclosure type: TS IT
	Enclosure type: TS: = 23.6 "
	Enclosure type: SE
	Enclosure type: CM
	Enclosure type: TP
	Enclosure type: PC
	Enclosure type: IW
	Enclosure type: TS IT
Packaging unit	2 pc(s).
Net weight	1.798
Gross weight	1.997
Customs tariff number	94039910
EAN	4028177208650
ECLASS 8.0	27182003

© Rittal 2025 3