

Rittal – The System.

Faster – better – everywhere.



TS 8601.060

Base/plinth trim panels, side, 100 mm

State: 7/4/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8601.060 - Base/plinth trim panels, side, 100 mm for base/plinth components, front and rear

To mount between the base/plinth components. For height 200 mm two 100 mm base/plinth trim panels can be used. Base/Plinth panels can be installed turned at 90° to provide stabilization for bayed base/plinth components.

Features

| | |
|---------------------|---|
| Model No. | TS 8601.060 |
| Product description | To mount between the base/plinth components. For height 200 mm, two 100 mm base/plinth trim panels can be used. |
| Material | Carbon steel |
| Surface finish | Spray-finished |
| Color | RAL 7022 |
| Supply includes | 2 plinth/base trim panels Assembly components |
| Mounting tip | 100 mm side trim panels can be installed rotated through 90° to provide stabilization for bayed base/plinth components. Base/plinth baying brackets are required here |
| Dimensions | Height: 100 mm Height: 3.94 " |

Features

| | |
|-----------------------|--|
| Suitable for | Enclosure type: TS: = 600 mm Enclosure type: SE Enclosure type: CM Enclosure type: TP Enclosure type: PC Enclosure type: IW Enclosure type: TS IT Enclosure type: TS: = 23.6 ″ Enclosure type: SE Enclosure type: CM Enclosure type: TP Enclosure type: PC Enclosure type: IW Enclosure type: TS IT |
| Packaging unit | 2 pc(s). |
| Net weight | 1.798 kg |
| Gross weight | 1.997 kg |
| Customs tariff number | 94039910 |
| ECLASS 8.0 | 27182003 |
| Product description | TS Trim panel, sides, H: 100 mm, for W: 600 mm, RAL 7022, sheet steel |