Rittal – The System.

Faster – better – everywhere.





TS 8601.600

Base/plinth components, front and rear, 100 mm

State: 10/26/2025 (Source: rittal.com/us-en)



TS 8601.600 - Base/plinth components, front and rear, 100 mm Carbon steel, for TS, TS IT, SE, CM, TP, PC, IW, TE

Base/Plinth component consisting of one trim panel and two pre-assembled corner pieces.

Features

Model No.	TS 8601.600
Version	Solid
Product description	Base/Plinth component consisting of one trim panel and two pre assembled corner pieces.
Material	Base/plinth components: Carbon steel Cover caps: Plastic
Surface finish	Spray-finished
Color	RAL 7022 Cover caps: RAL 9005
Supply includes	2 base/plinth components 4 cover caps Assembly components
Dimensions	Height: 100 mm Height: 3.94 ″
Suitable for	Enclosure type: TS: = 600 mm Enclosure type: SE Enclosure type: CM Enclosure type: TP Enclosure type: PC Enclosure type: TS IT Enclosure type: TS: = 23.6 " Enclosure type: SE Enclosure type: CM Enclosure type: TP Enclosure type: TP Enclosure type: TP Enclosure type: PC Enclosure type: IW Enclosure type: TS IT

© Rittal 2025 2

Features

Packaging unit	2 pc(s).
Net weight	3.7
Gross weight	4.168
Customs tariff number	94039910
EAN	4028177208568
ECLASS 8.0	27182003

© Rittal 2025 3