

**Rittal – The System.**

Faster – better – everywhere.



**TS 8601.920**

**Base/plinth components, front and rear, 100 mm**

State: 6/10/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8601.920 - Base/plinth components, front and rear, 100 mm Carbon steel, for TS, TS IT, SE, CM, TP, PC, IW, TE

Base/Plinth component consisting of one trim panel and two pre-assembled corner pieces.

## Features

Model No.	TS 8601.920
Version	Solid
Product description	Base/Plinth component consisting of one trim panel and two pre-assembled corner pieces.
Material	Base/plinth components: Carbon steel Cover caps: Plastic
Surface finish	Spray-finished
Color	RAL 7022 Cover caps: RAL 9005
Supply includes	2 base/plinth components 4 cover caps Assembly components
Dimensions	Height: 100 mm Height: 3.94 "
Suitable for	Enclosure type: TS: = 1,600 mm Enclosure type: SE Enclosure type: CM Enclosure type: TP Enclosure type: PC Enclosure type: IW Enclosure type: TS IT Enclosure type: TS: = 63 " Enclosure type: SE Enclosure type: CM Enclosure type: TP Enclosure type: PC Enclosure type: IW Enclosure type: TS IT

# Features

---

Packaging unit	2 pc(s).
Net weight	8.232 kg
Gross weight	8.666 kg
Customs tariff number	94039910
ECLASS 8.0	27182003
Product description	TS Base/plinth component, front and rear, H: 100 mm, for W: 1600 mm, RAL 7022, sheet steel