Rittal – The System.

Faster – better – everywhere.





TS 8602.060

Base/plinth trim panels, side, 200 mm

State: 11/17/2025 (Source: rittal.com/us-en)



TS 8602.060 - Base/plinth trim panels, side, 200 mm for base/plinth components, front and rear

To mount between the base/plinth components. For height 200 mm two 100 mm base/plinth trim panels can be used.

Features

Model No.	TS 8602.060
Product description	To mount between the base/plinth components. For height 200 mm, two 100 mm base/plinth trim panels can be used.
Material	Carbon steel
Surface finish	Spray-finished
Color	RAL 7022
Supply includes	2 plinth/base trim panels Assembly components
Mounting tip	100 mm side trim panels can be installed rotated through 90° to provide stabilization for bayed base/plinth components. Base/plinth baying brackets are required here
Dimensions	Height: 200 mm Height: 7.87 "
Suitable for	Enclosure type: TS: = 600 mm Enclosure type: SE Enclosure type: CM Enclosure type: TP Enclosure type: PC Enclosure type: IW Enclosure type: TS IT Enclosure type: TS: = 23.6 " Enclosure type: SE Enclosure type: CM Enclosure type: TP Enclosure type: TP Enclosure type: PC Enclosure type: IW Enclosure type: IW Enclosure type: TS IT

© Rittal 2025

Features

Packaging unit	2 pc(s).
Net weight	3.186
Gross weight	3.385
Customs tariff number	94039910
EAN	4028177208698
ECLASS 8.0	27182003

© Rittal 2025 3