
### Rittal – The System.

Faster – better – everywhere.





### TS 8602.080

# Base/plinth trim panels, side, 200 mm

State: 11/24/2025 (Source: rittal.com/us-en)



## TS 8602.080 - Base/plinth trim panels, side, 200 mm for base/plinth components, front and rear

To mount between the base/plinth components. For height 200 mm two 100 mm base/plinth trim panels can be used.

#### **Features**

Model No.	TS 8602.080
Product description	To mount between the base/plinth components. For height 200 mm two 100 mm base/plinth trim panels can be used.
Material	Carbon steel
Surface finish	Spray-finished
Color	RAL 7022
Supply includes	2 plinth/base trim panels Assembly components
Mounting tip	100 mm side trim panels can be installed rotated through 90° to provide stabilization for bayed base/plinth components. Base/plinth baying brackets are required here
Dimensions	Height: 200 mm Height: 7.87 ˝
Suitable for	Enclosure type: TS: = 800 mm  Enclosure type: SE  Enclosure type: CM  Enclosure type: TP  Enclosure type: PC  Enclosure type: IW  Enclosure type: TS IT  Enclosure type: TS: = 31.5 ~  Enclosure type: SE  Enclosure type: CM  Enclosure type: TP  Enclosure type: TP  Enclosure type: PC  Enclosure type: IW  Enclosure type: IW  Enclosure type: TS IT

© Rittal 2025 2

### **Features**

Packaging unit	2 pc(s).
Net weight	4.454
Gross weight	4.654
Customs tariff number	94039910
EAN	4028177208704
ECLASS 8.0	27182003

© Rittal 2025 3