

**Rittal – The System.**

Faster – better – everywhere.



**TS 8602.400**

**Base/plinth components, front and rear, 200 mm**

State: 4/2/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8602.400 - Base/plinth components, front and rear, 200 mm Carbon steel, for TS, TS IT, SE, CM, TP, PC, IW, TE

Base/Plinth component consisting of one trim panel and two pre-assembled corner pieces. On 200 mm high base/plinth components, one trim panel is in two parts to allow for cable entry.

## Features

|                     |   |
|---------------------|---|
| Model No.           | TS 8602.400   |
| Version             | Solid   |
| Product description | Base/Plinth component consisting of one trim panel and two pre-assembled corner pieces. On 200 mm high base/plinth components, one trim panel is in two parts to allow for cable entry. |
| Material            | Base/plinth components: Carbon steel<br>Cover caps: Plastic   |
| Surface finish      | Spray-finished  |
| Color               | RAL 7022<br>Cover caps: RAL 9005  |
| Supply includes     | 2 base/plinth components<br>4 cover caps<br>Assembly components   |
| Dimensions          | Height: 200 mm<br>Height: 7.87 "  |

# Features

---

|                       |  |
|-----------------------|--|
| Suitable for          | Enclosure type: TS: = 400 mm<br>Enclosure type: SE<br>Enclosure type: CM<br>Enclosure type: TP<br>Enclosure type: PC<br>Enclosure type: IW<br>Enclosure type: TS IT<br>Enclosure type: TS: = 15.7 "<br>Enclosure type: SE<br>Enclosure type: CM<br>Enclosure type: TP<br>Enclosure type: PC<br>Enclosure type: IW<br>Enclosure type: TS IT |
| Packaging unit        | 2 pc(s).   |
| Net weight            | 4.54 kg  |
| Gross weight          | 5.622 kg   |
| Customs tariff number | 94039910   |
| ECLASS 8.0            | 27182003   |
| Product description   | TS Base/plinth component, front and rear, H: 200 mm, for W: 400 mm, RAL 7022, sheet steel  |