Rittal – The System.

Faster – better – everywhere.





TS 8606.548 Baying systems TS 8

State: 10/16/2025 (Source: rittal.com/us-en)



TS 8606.548 - Baying systems TS 8 Type 3R

Rittal perfected the concept of the industrial modular enclosure with the TS 8 series. These single door, UL Type 3R rated enclosures consist of a frame with door, rear wall, and roof plate. Purchase sidewalls and plinth separately for complete assembly.

Features

TS 8606.548
Enclosure frame: Carbon steel, 1.5 mm
Roof: Carbon steel, 1.5 mm
Door: Carbon steel, 2.0 mm
Rear wall: carbon steel, 1.5 mm
Mounting panel: Carbon steel, 3.0 mm
Enclosure frame: powder-coated
Door, roof and rear panel: Dipcoat-primed, powder-coated on the
outside, textured paint
Mounting plate and base plates: Zinc-plated
RAL 7035
Enclosure frame with door(s)
Roof plate
Rear panel, detachable
4 eyebolts
Base Plates
Mounting plate
Width: 600 mm
Height: 2,000 mm
Depth: 600 mm
Width: 23.6 "
Height: 78.7 "
Depth: 23.6 "
NEMA 3R
1 pc(s).
221.997

© Rittal 2025 2

Features

Customs tariff number	7326909099
UPC-Code	85178

Approvals

Approvals UL + C-UL (listed)	
------------------------------	--

© Rittal 2025 3