

Rittal – The System.

Faster – better – everywhere.



TS 8610.605 Glazed Door

State: 8/17/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8610.605 - Glazed Door for TS, TS IT, VX SE

Alternative to a carbon steel door or rear wall.



Features

Model No.	TS 8610.605
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminum section Corner pieces: Die-cast zinc Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	Frame: RAL 7035 Corner pieces: RAL 7035 Viewing window (printed mask on the inside): RAL 9005
Supply includes	Glazed door frame with safety glass Locking rod with double-bit insert 180° hinges (4 pcs)
Visible area	Viewing window width: 460 mm Viewing window height: 1,840 mm Viewing window width: 18.1 " Viewing window height: 72.4 "

Features

Viewing window height	1,840 mm 72.4 "
Mounting tip	When mounting instead of the rear panel, the lock components are required
Protection category IP to IEC 60529	IP 55
Suitable for	Enclosure type: TS TS IT VX SE Width: = 600 mm Height: = 2,000 mm Enclosure type: TS TS IT VX SE Width: = 23.6 " Height: = 78.7 "
Packaging unit	1 pc(s).
Net weight	10.5
Gross weight	12.5
EAN	4028177693845
ETIM 9	EC000747
ECLASS 8.0	27182204