Rittal – The System.

Faster – better – everywhere.



TS 8610.625 Glazed Door

State: 11/8/2025 (Source: rittal.com/us-en)



TS 8610.625 - Glazed Door for TS, TS IT, VX SE

Alternative to a carbon steel door or rear wall.



Features

| Model No. | TS 8610.625 |
|---------------------|---|
| Product description | Instead of a sheet steel door or rear panel. |
| Material | Frame: Extruded aluminum section |
| | Corner pieces: Die-cast zinc |
| | Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| Color | Frame: RAL 7035 |
| | Corner pieces: RAL 7035 |
| | Viewing window (printed mask on the inside): RAL 9005 |
| Supply includes | Glazed door frame with safety glass |
| | Locking rod with double-bit insert |
| | 180° hinges (4 pcs) |
| Visible area | Viewing window width: 460 mm |
| | Viewing window height: 2,040 mm |
| | Viewing window width: 18.1 " |
| | Viewing window height: 80.3 " |

© Rittal 2025

Features

| Viewing window height | 2,040 mm 80.3 ″ |
|--------------------------------------|---|
| Mounting tip | When mounting instead of the rear panel, the lock components are required |
| Protection category IP to IEC 60 529 | IP 55 |
| Suitable for | Enclosure type: TS TS IT VX SE Width: = 600 mm Height: = 2,200 mm Enclosure type: TS TS IT VX SE Width: = 23.6 " Height: = 86.6 " |
| Packaging unit | 1 pc(s). |
| Net weight | 15.7 |
| Gross weight | 16.2 |
| EAN | 4028177693869 |
| ETIM 9 | EC000747 |
| ECLASS 8.0 | 27182204 |

© Rittal 2025 3