

Rittal – The System.

Faster – better – everywhere.



TS 8610.825 Glazed Door

State: 6/10/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8610.825 - Glazed Door for TS, TS IT, VX SE

Alternative to a carbon steel door or rear wall.



Features

| | |
|---------------------|--|
| Model No. | TS 8610.825 |
| Product description | Instead of a sheet steel door or rear panel. |
| Material | Frame: Extruded aluminum section Corner pieces: Die-cast zinc Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| Color | Frame: RAL 7035 Corner pieces: RAL 7035 Viewing window (printed mask on the inside): RAL 9005 |
| Supply includes | Glazed door frame with safety glass Locking rod with double-bit insert 180° hinges (4 pcs) |
| Visible area | Viewing window width: 660 mm Viewing window height: 2,040 mm Viewing window width: 26 ″ Viewing window height: 80.3 ″ |

Features

| | |
|-------------------------------------|--|
| Viewing window height | 2,040 mm 80.3 " |
| Mounting tip | When mounting instead of the rear panel, the lock components are required |
| Protection category IP to IEC 60529 | IP 55 |
| Suitable for | Enclosure type: TS TS IT VX SE Width: = 800 mm Height: = 2,200 mm Enclosure type: TS TS IT VX SE Width: = 31.5 " Height: = 86.6 " |
| Packaging unit | 1 pc(s). |
| Net weight | 19 kg |
| Gross weight | 20 kg |
| Customs tariff number | 76101000 |
| ETIM 9 | EC000747 |
| ECLASS 8.0 | 27182204 |
| Product description | TS Glazed door, for TS, TS IT, SE, for WH: 800x2200 mm |