Rittal – The System.

Faster – better – everywhere.



TS 8610.885 Glazed Door

State: 11/17/2025 (Source: ritial.com/us-en)



TS 8610.885 - Glazed Door for TS, TS IT, VX SE

Alternative to a carbon steel door or rear wall.



Features

Model No.	TS 8610.885
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminum section
	Corner pieces: Die-cast zinc
	Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	Frame: RAL 7035
	Corner pieces: RAL 7035
	Viewing window (printed mask on the inside): RAL 9005
Supply includes	Glazed door frame with safety glass
	Locking rod with double-bit insert
	180° hinges (4 pcs)
Visible area	Viewing window width: 660 mm
	Viewing window height: 1,640 mm
	Viewing window width: 26 "
	Viewing window height: 64.6 "

© Rittal 2025

Features

Viewing window height	1,640 mm
The state of the s	64.6 "
Mounting tip	When mounting instead of the rear panel, the lock components are required
Protection category IP to IEC 60 529	IP 55
Suitable for	Enclosure type: TS
	TS IT
	VX SE
	Width: = 800 mm
	Height: = 1,800 mm
	Enclosure type: TS
	TS IT
	VX SE
	Width: = 31.5 "
	Height: = 70.9 "
Packaging unit	1 pc(s).
Net weight	14.77
Gross weight	15.6
EAN	4028177693838
ETIM 9	EC000747
ECLASS 8.0	27182204

© Rittal 2025 3