
Rittal – The System.

Faster – better – everywhere.



TS 8612.520

TS System Chassis 23 x 73 mm


State: 11/13/2026 (Source: www.rittal.com/us-en)


ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TS 8612.520 - TS System Chassis 23 x 73 mm

The alternative to the TS 17 x 73 mm system chassis, with punchings for captive nuts/speed nuts instead of slotted holes top and bottom. Simply locate and secure.





Features

Model No.	TS 8612.520
Product description	The alternative to the TS 17 x 73 mm system chassis, with punchings for captive nuts/speed nuts instead of slotted holes top and bottom. Simply locate and secure.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Installation options	On the vertical TS, VX SE enclosure section
Suitable for	Enclosure type: the inner mounting level Width/depth: 1,200 mm Enclosure type: the inner mounting level Width/depth: 47.2 ˝
Packaging unit	4 pc(s).
Net weight	5.128 kg
Gross weight	5.396 kg
Customs tariff number	73269098
ETIM 9	EC002625
ECLASS 8.0	27189234

Features

Product description	TS TS punched section with mounting flange, 23 x 73 mm, for inner mounting level: W/D: 1200 mm