
## Rittal – The System.

Faster – better – everywhere.





TS 8612.650

# TS Mounting Chassis, 45 x 88 mm

State: 11/17/2025 (Source: rittal.com/us-en)



## TS 8612.650 - TS Mounting Chassis, 45 x 88 mm

Mounted directly on internal surfaces (e.g. roof) to support heavy assemblies. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine.



#### **Features**

Model No.	TS 8612.650
Version	For the inner mounting level
Product description	Mounted directly on internal surfaces (e.g. roof) to support heavy assemblies. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine. The double profile with 11 rows of holes provides many additional options for interior configuration.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Installation options	On the vertical and horizontal TS, VX SE enclosure section
Suitable for	Enclosure type: the inner mounting level Suitable for width/depth: 500 mm Enclosure type: the inner mounting level Suitable for width/depth: 19.7 "
Packaging unit	2 pc(s).
Net weight	2.6
Gross weight	2.611
Customs tariff number	73269098

© Rittal 2025

#### **Features**

EAN	4028177267053
ETIM 9	EC002625
ECLASS 8.0	27189234

© Rittal 2025 3