



Rittal – The System.

Faster – better – everywhere.



TS 8612.660

TS Mounting Chassis, 45 x 88 mm


State: 2/4/2026 (Source: rittal.com/us-en)



FRIEDHELM LOH GROUP

TS 8612.660 - TS Mounting Chassis, 45 x 88 mm

Mounted directly on internal surfaces (e.g. roof) to support heavy assemblies. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine.



Features

Model No.	TS 8612.660
Version	For the inner mounting level
Product description	Mounted directly on internal surfaces (e.g. roof) to support heavy assemblies. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine. The double profile with 11 rows of holes provides many additional options for interior configuration.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Installation options	On the vertical and horizontal TS, VX SE enclosure section
Suitable for	Enclosure type: the inner mounting level Width/depth: 600 mm Enclosure type: the inner mounting level Width/depth: 23.6 "
Packaging unit	2 pc(s).
Net weight	2.8
Gross weight	3.02
Customs tariff number	73269098

Features

EAN 4028177267060

ETIM 9 EC002625

ECLASS 8.0 27189234