

Rittal – The System.

Faster – better – everywhere.



TS 8612.680

TS Mounting Chassis, 45 x 88 mm

State: 6/7/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.680 - TS Mounting Chassis, 45 x 88 mm

Mounted directly on internal surfaces (e.g. roof) to support heavy assemblies. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine.



Features

| | |
|-----------------------|---|
| Model No. | TS 8612.680 |
| Version | For the inner mounting level |
| Product description | Mounted directly on internal surfaces (e.g. roof) to support heavy assemblies. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine. The double profile with 11 rows of holes provides many additional options for interior configuration. |
| Material | Carbon steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly components |
| Installation options | On the vertical and horizontal TS, VX SE enclosure section |
| Suitable for | Enclosure type: the inner mounting level Width/depth: 800 mm Enclosure type: the inner mounting level Width/depth: 31.5 " |
| Packaging unit | 2 pc(s). |
| Net weight | 3.638 kg |
| Gross weight | 3.837 kg |
| Customs tariff number | 73269098 |

Features

| | |
|---------------------|---|
| ETIM 9 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | TS TS punched section without mounting flange, 45 x 88 mm, for inner mounting level: for WD: 800 mm |
