

**Rittal – The System.**

Faster – better – everywhere.



**TS 8612.760**

**TS punched rail, 25 x 38 mm**

State: 4/2/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8612.760 - TS punched rail, 25 x 38 mm

For heavy installed equipment, with mounting holes. Installation options on the vertical TS enclosure profile.



## Features

Model No.	TS 8612.760
Product description	For heavy installed equipment, with mounting holes.
Material	Carbon steel, 3.0 mm
Surface finish	Zinc-plated
Supply includes	Assembly screws
Installation options	On the vertical TS, VX SE enclosure section With 9 mm round holes all round on a 25 mm hole pattern For the external mounting of support rails, system support rails, C rails 30/15, cable clamp rails (angle section) and own assemblies
Note	In conjunction with the snap-on nut, particularly well-suited for dynamic connections
Suitable for	Width/depth: 600 mm Width/depth: 23.6 "
Packaging unit	2 pc(s).
Net weight	1.648 kg
Gross weight	1.96 kg
Customs tariff number	73269098
ECLASS 8.0	27189261

# Features

---

Product description

TS Punched rail 25 x 38 mm, for WD: 600 mm