

Rittal – The System.

Faster – better – everywhere.



TS 8612.780

TS punched rail, 25 x 38 mm

State: 5/16/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.780 - TS punched rail, 25 x 38 mm

For heavy installed equipment, with mounting holes. Installation options on the vertical TS enclosure profile.



Features

Model No.	TS 8612.780
Product description	For heavy installed equipment, with mounting holes.
Material	Carbon steel, 3.0 mm
Surface finish	Zinc-plated
Supply includes	Assembly screws
Installation options	On the vertical TS, VX SE enclosure section With 9 mm round holes all round on a 25 mm hole pattern For the external mounting of support rails, system support rails, C rails 30/15, cable clamp rails (angle section) and own assemblies
Note	In conjunction with the snap-on nut, particularly well-suited for dynamic connections
Suitable for	Suitable for width/depth: 800 mm Suitable for width/depth: 31.5 "
Packaging unit	2 pc(s).
Net weight	2.488
Gross weight	2.687
Customs tariff number	73269098
EAN	4028177429154

Features

ETIM 9	EC002620
ECLASS 8.0	27189261