



Rittal – The System.

Faster – better – everywhere.



VX 8619.750

System chassis 14 x 39 mm

State: 6/17/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.750 - System chassis 14 x 39 mm for VX, VX SE, PC, IW, AX

For securing cable ducts, cable conduit holders, equipment installed on the door, etc.



Features

Model No.	VX 8619.750
Product description	For securing cable ducts, cable conduit holders, equipment installed on the door, etc.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Distance between fixing points	875 mm
Suitable for door width	1,000 mm 39.4 "
Installation options VX SE	In door width 900 mm
Installation options AX stainless steel	In enclosure height 1000 mm
Mounting tip	For installation in AX carbon steel, only in conjunction with rails interior installation AX
Note	Carbon steel screws or M5 self-tapping screws are required for extension with own components on the system chassis

Features

Suitable for	Enclosure type: VX SE AX stainless steel Suitable for width or height or depth: 1,000 mm
Packaging unit	4 pc(s).
Net weight	1.776 kg
Gross weight	2.06 kg
PCF/VE (cradle-to-gate)	13.6
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189234
Product description	VX Punched section, with mounting flange 14 x 39 mm, for door width:1000 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------