

Rittal – The System.

Faster – better – everywhere.



VX 8620.014

**Base/plinth corner pieces with
base/plinth trim panels, front and
rear, 100 mm**

State: 3/14/2026 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8620.014 - Base/plinth corner pieces with base/plinth trim panels, front and rear, 100 mm for VX, VX IT, VX SE, TE, TS, TS IT, TP, PC, IW

Base/plinth corner pieces with molded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for best access to the screw-fastening point can be covered using bay and corner covers.

Features

Model No.	VX 8620.014
Product description	Base/plinth corner pieces with molded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for best access to the screw-fastening point can be covered using bay and corner covers.
Material	Base/plinth corner piece: Carbon steel Base/plinth trim panels, front/rear: Carbon steel Corner and baying covers: Plastic
Color	RAL 9005
Supply includes	4 x base/plinth corner pieces, 100 mm high 4 x corner covers 1 x baying cover 2 x base/plinth trim panels, front/rear, 100 mm high Assembly components
Note	Base/plinth trim panels, on the side for closing off a base/plinth unit, for additional stabilization of the bases/plinths to one another, or for interior installation of the bases/plinths
Dimensions	Height: 100 mm Height: 3.94 "

Features

Suitable for	Enclosure type: VX Width: = 700 mm Enclosure type: VX Width: = 27.6 "
Packaging unit	2 pc(s).
Customs tariff number	94039910
ECLASS 8.0	27182003
Product description	VX base/plinth corner piece with base/plinth trim panel, front and rear, H = 100 mm, for W: 700 mm

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------