


Rittal – The System.

Faster – better – everywhere.



VX 8620.095

Base/Plinth Trim Panels with Brush Strip

State: 1/31/2026 (Source: rittal.com/us-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 8620.095 - Base/Plinth Trim Panels with Brush Strip

For VX base/plinth systems

The 100 mm high base/plinth trim panels can be used in the depth or the width for cable entry into the base/plinth. The trim panels can also be used in 200 mm high base/plinths and they can be combined with other 100 mm high trim panels.

Features

Model No.	VX 8620.095
Product description	For cable entry into the base/plinth. If the base/plinth height is 200 mm, one or two trim panels with brush strips can optionally be used. The VX base/plinth system's complete symmetry allows the trim panels with brush strips to be mounted either at the front, rear or side of the base/plinth corner piece.
Material	Base/plinth trims: Carbon steel Brush strip: Plastic, self-extinguishing
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 100 mm Height: 3.94 "
Suitable for	Width/depth: 1,200 mm Width/depth: 47.2 "
Type rating according to UL 50E	Type 1, 12
Weight/packaging unit	2.8 kg 6.2 lb.
Packaging unit	2 pc(s).
Net weight	2.5
Gross weight	2.8
Customs tariff number	94039910
EAN	4028177922488
ETIM 9	EC000721

Features

ECLASS 8.0

27182003

Approvals

Approvals

UL + C-UL - FTTA