Rittal – The System.

Faster – better – everywhere.



VX 8640.032

Base/plinth trim panels, side, 100 mm

State: 11/15/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 8640.032 - Base/plinth trim panels, side, 100 mm for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.

Features

Model No.	VX 8640.032
Product description	For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 100 mm Height: 3.94 ″
Suitable for	Depth: = 500 mm Depth: = 19.7 ″
Type rating according to 508A	Type 1, 12
Weight/packaging unit	1.36 kg 3 lb.
Packaging unit	2 pc(s).
Net weight	1.16 kg
Gross weight	1.36 kg
Customs tariff number	94039910
ETIM 9	EC000721
ECLASS 8.0	27182003

© Rittal 2026

Features

Product description	VX Base/plinth trim panel, side, H: 100 mm, for D: 500 mm, sheet steel

Approvals

Approvals	UL + C-UL - FTTA