Rittal – The System.

Faster – better – everywhere.



VX 8640.033

Base/plinth trim panels, side, 100 mm

State: 11/19/2026 (Source: www.rittal.com/us-en)

VX 8640.033 - Base/plinth trim panels, side, 100 mm for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.

Features

Model No.	VX 8640.033
Product description	For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 100 mm Height: 3.94 ″
Suitable for	Enclosure type: VX TX CableNet Depth: = 600 mm Enclosure type: VX TX CableNet Depth: = 23.6 ″
Type rating according to 508A	Type 1, 12
Weight/packaging unit	1.78 kg 3.9 lb.
Packaging unit	2 pc(s).
Net weight	1.65 kg
Gross weight	1.73 kg
Customs tariff number	94039910

Features

ETIM 9	EC000721
ECLASS 8.0	27182003
Product description	VX Base/plinth trim panel, side, H: 100 mm, for D: 600 mm, sheet steel

Approvals

Approvals	UL + C-UL - FTTA