

**Rittal – The System.**

Faster – better – everywhere.



**VX 8640.033**

Base/plinth trim panels, side, 100  
mm

State: 2/2/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# VX 8640.033 - Base/plinth trim panels, side, 100 mm for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.

## Features

|                                 |  |
|---------------------------------|--|
| Model No.                       | VX 8640.033  |
| Product description             | For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths. |
| Material                        | Carbon steel   |
| Color                           | RAL 9005   |
| Supply includes                 | Assembly components  |
| Dimensions                      | Height: 100 mm<br>Height: 3.94 "   |
| Suitable for                    | Enclosure type: VX<br>TX CableNet<br>Depth: = 600 mm<br>Enclosure type: VX<br>TX CableNet<br>Depth: = 23.6 "   |
| Type rating according to UL 50E | Type 1, 12   |
| Weight/packaging unit           | 1.78 kg<br>3.9 lb.   |
| Packaging unit                  | 2 pc(s).   |
| Net weight                      | 1.65   |
| Gross weight                    | 1.73   |
| Customs tariff number           | 94039910   |

# Features

---

EAN 4028177958951

E-Number Sweden E3465379

ETIM 9 EC000721

ECLASS 8.0 27182003

# Approvals

---

Approvals UL + C-UL - FTTA