

# Rittal – The System.

Faster – better – everywhere.



## VX 8640.034

## Base/plinth trim panels, side, 100 mm

State: 6/12/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8640.034 - Base/plinth trim panels, side, 100 mm for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.

## Features

Model No.	VX 8640.034
Product description	For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 100 mm Height: 3.94 "
Suitable for	Enclosure type: VX TX CableNet Depth: = 800 mm Enclosure type: VX TX CableNet Depth: = 31.5 "
Type rating according to UL 50E	Type 1, 12
Weight/packaging unit	2.54 kg 5.6 lb.
Packaging unit	2 pc(s).
Net weight	2.14
Gross weight	2.52
Customs tariff number	94039910

# Features

EAN	4028177958968
E-Number Sweden	E3465380
ETIM 9	EC000721
ECLASS 8.0	27182003

# Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------