Rittal – The System.

Faster – better – everywhere.





VX 8640.035 Base/plinth trim panels, side, 100 mm

State: 11/16/2025 (Source: rittal.com/us-en)



VX 8640.035 - Base/plinth trim panels, side, 100 mm for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.

Features

Model No.	VX 8640.035
Product description	For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 100 mm Height: 3.94 ″
Suitable for	Enclosure type: VX TX CableNet Depth: = 1,000 mm Enclosure type: VX TX CableNet Depth: = 39.4 "
Type rating according to UL 50E	Type 1, 12
Weight/packaging unit	3.3 kg 7.3 lb.
Packaging unit	2 pc(s).
Net weight	2.442
Gross weight	3.382
Customs tariff number	94039910

© Rittal 2025 2

Features

EAN	4028177958975
E-Number Sweden	E3465381
ETIM 9	EC000721
ECLASS 8.0	27182003

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025 3