

Rittal – The System.

Faster – better – everywhere.



VX 8640.036

Base/plinth trim panels, side, 100 mm

State: 6/10/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8640.036 - Base/plinth trim panels, side, 100 mm for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.



Features

Model No.	VX 8640.036
Product description	For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 100 mm Height: 3.94 "
Suitable for	Depth: = 1,200 mm Depth: = 47.2 "
Type rating according to UL 50E	Type 1, 12
Weight/packaging unit	4.12 kg 9.1 lb.
Packaging unit	2 pc(s).
Net weight	3.7 kg
Gross weight	3.94 kg

Features

Customs tariff number	94039910
ETIM 9	EC000721
ECLASS 8.0	27182003
Product description	VX Base/plinth trim panel, side, H: 100 mm, for D: 1200 mm, sheet steel

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------