

Rittal – The System.

Faster – better – everywhere.



VX 8640.042

Base/plinth trim panels, side, 200 mm

State: 6/13/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8640.042 - Base/plinth trim panels, side, 200 mm for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and for additional stabilization or the interior installation of baying bases. One 200 mm-high or two 100 mm-high trim panels can optionally be fitted on 200 mm-high base/plinths.

Features

Model No.	VX 8640.042
Product description	For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 200 mm Height: 7.87 "
Suitable for	Depth: = 500 mm Depth: = 19.7 "
Type rating according to UL 50E	Type 1 Type 12
Weight/packaging unit	2.32 kg 5.1 lb.
Packaging unit	2 pc(s).
Net weight	2.32 kg
Gross weight	2.32 kg
Customs tariff number	94039910
ETIM 9	EC000721
ECLASS 8.0	27182003

Features

Product description

VX Base/plinth trim panel, side, H: 200 mm, for D: 500 mm, sheet steel

Approvals

Approvals

UL + C-UL - FTTA