Rittal – The System.

Faster – better – everywhere.





VX 8640.043 Base/plinth trim panels, side, 200 mm

State: 11/16/2025 (Source: rittal.com/us-en)



VX 8640.043 - Base/plinth trim panels, side, 200 mm for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and for additional stabilization or the interior installation of baying bases. One 200 mm-high or two 100 mm-high trim panels can optionally be fitted on 200 mm-high base/plinths.

Features

Model No.	VX 8640.043
Product description	For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 200 mm Height: 7.87 ″
Suitable for	Depth: = 600 mm Depth: = 23.6 "
Type rating according to UL 50E	Type 1 Type 12
Weight/packaging unit	3 kg 6.6 lb.
Packaging unit	2 pc(s).
Net weight	2.8
Gross weight	2.98
Customs tariff number	94039910
EAN	4028177959040
E-Number Sweden	E3465386

© Rittal 2025 2

Features

ETIM 9	EC000721
ECLASS 8.0	27182003

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025 3