

Rittal – The System.

Faster – better – everywhere.



VX 8640.045

Base/plinth trim panels, side, 200
mm

State: 1/30/2026 (Source: rittal.com/us-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 8640.045 - Base/plinth trim panels, side, 200 mm for base/plinth system VX, carbon steel

For side blanking of a base/plinth unit and for additional stabilization or the interior installation of baying bases. One 200 mm-high or two 100 mm-high trim panels can optionally be fitted on 200 mm-high base/plinths.

Features

Model No.	VX 8640.045
Product description	For side blanking of a base/plinth unit and additional stability, or the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels can optionally be fitted on 200 mm high base/plinths.
Material	Carbon steel
Color	RAL 9005
Supply includes	Assembly components
Dimensions	Height: 200 mm Height: 7.87 "
Suitable for	Depth: = 1,000 mm Depth: = 39.4 "
Type rating according to UL 50E	Type 1 Type 12
Weight/packaging unit	5.58 kg 12.3 lb.
Packaging unit	2 pc(s).
Net weight	5.08
Gross weight	5.18
Customs tariff number	94039910
EAN	4028177959064
E-Number Sweden	E3465388

Features

ETIM 9 EC000721

ECLASS 8.0 27182003

Approvals

Approvals UL + C-UL - FTTA