## Rittal - The System.

Faster – better – everywhere.





## TS 8701.050 Base/plinth trim panels, side, 100 mm

State: 11/1/2025 (Source: rittal.com/us-en)



## TS 8701.050 - Base/plinth trim panels, side, 100 mm Stainless steel for base/plinth components front and rear

To mount between the base/plinth components. For height 200 mm, two 100 mm base/plinth trim panels can be used. Base/Plinth panels can be installed turned through 90° to provide stabilization for bayed base/plinth components.

## **Features**

Model No.	TS 8701.050
Product description	To mount between the base/plinth components. For height 200 mm, two 100 mm base/plinth trim panels can be used.
Material	Stainless steel 1.4301 (AISI 304)
Surface finish	Brushed, grain 400
Supply includes	2 plinth/base trim panels Assembly components
Mounting tip	100 mm side trim panels can be installed rotated through 90° to provide stabilization for bayed base/plinth components. Base/plinth baying brackets are required here
Dimensions	Height: 100 mm Height: 3.94 ″
Suitable for	Enclosure type: TS: = 500 mm Enclosure type: TS: = 19.7 ″
Packaging unit	2 pc(s).
Net weight	2.002
Gross weight	2.202
Customs tariff number	94039910
EAN	4028177300071
ETIM 9	EC000721
ECLASS 8.0	27182003

© Rittal 2025 2