

Rittal – The System.

Faster – better – everywhere.



TS 8800.540

Cable duct

State: 1/24/2026 (Source: rittal.com/us-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TS 8800.540 - Cable duct for vertical TS section

For mounting on a vertical enclosure profile or on two bayed enclosure profiles in the baying area.



Features

Model No.	TS 8800.540
Version	Width 100 mm, for assembly on two bayed enclosure sections in the baying area.
Benefits	<p>The cable duct fastening points are co-ordinated with the TS system hole pattern. This eliminates time-consuming drilling work that would be necessary with DIN ducts.</p> <p>The nominal break points of the bars are also designed in combination with the cable ducts for mounting plates.</p> <p>A further nominal break at the mounting plate height allows direct entry to the cable duct.</p>
Material	Hard PVC Flame-resistant, self-extinguishing
Color	Similar to RAL 7030
Supply includes	Cable duct with cover
Bar width	5.5 mm 0.22 "
Slot width	4.5 mm 0.18 "
Note	Can be shortened for other enclosure sizes.

Features

Dimensions	Width: 100 mm Height: 1,600 mm Depth: 80 mm Width: 3.94 " Height: 63 " Depth: 3.15 "
Suitable for	Enclosure type: TS VX SE PC IW Height: ≤ 1,800 mm Enclosure type: TS VX SE PC IW Height: ≤ 70.9 "
Operating temperature range	60 °C 140 °F
Packaging unit	4 pc(s).
Net weight	8.192
Gross weight	8.623
Customs tariff number	73269098
EAN	4028177238008
ECLASS 8.0	27400703

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---