## Rittal – The System.

Faster – better – everywhere.





# TS 8800.570 Cable duct

State: 11/2/2025 (Source: rittal.com/us-en)



### TS 8800.570 - Cable duct for vertical TS section

For mounting on a vertical enclosure profile or on two bayed enclosure profiles in the baying area.







#### **Features**

Model No.	TS 8800.570
Version	Width 50 mm, for assembly on a vertical enclosure section in the side panel area.
Benefits	The cable duct fastening points are co-ordinated with the TS system hole pattern. This eliminates time-consuming drilling work that would be necessary with DIN ducts.  The nominal break points of the bars are also designed in combination with the cable ducts for mounting plates.  A further nominal break at the mounting plate height allows direct entry to the cable duct.
Material	Hard PVC Flame-resistant, self-extinguishing
Color	Similar to RAL 7030
Supply includes	Cable duct with cover
Bar width	5.5 mm 0.22 ″
Slot width	4.5 mm 0.18 ″
Note	Can be shortened for other enclosure sizes.

© Rittal 2025

## Features

Dimensions	Width: 50 mm
	Height: 1,600 mm
	Depth: 80 mm
	Width: 1.97 "
	Height: 63 "
	Depth: 3.15 "
Suitable for	Enclosure type: TS
	VX SE
	PC
	IW
	Height: ≤ 1,800 mm
	Enclosure type: TS
	VX SE
	PC
	IW
	Height: ≤ 70.9 "
Operating temperature range	60 °C
	140 °F
Packaging unit	8 pc(s).
Net weight	8.968
Gross weight	9.44
Customs tariff number	39259020
EAN	4028177238015
ETIM 9	EC000012
ECLASS 8.0	27400703

# Approvals

Explanations	Declaration of conformity	
	Declaration of conformity UK	

© Rittal 2025 3