Rittal – The System.

Faster – better – everywhere.



TS 8800.570

Cable duct

State: 10/31/2026 (Source: www.rittal.com/us-en)

TS 8800.570 - Cable duct for vertical TS section

For mounting on a vertical enclosure profile or on two bayed enclosure profiles in the baying area.







Features

Model No.	TS 8800.570
Version	Width 50 mm, for assembly on a vertical enclosure section in the side panel area.
Benefits	The cable duct fastening points are co-ordinated with the TS system hole pattern. This eliminates time-consuming drilling work that would be necessary with DIN ducts. The nominal break points of the bars are also designed in combination with the cable ducts for mounting plates. A further nominal break at the mounting plate height allows direct entry to the cable duct.
Material	Hard PVC Flame-resistant, self-extinguishing
Color	Similar to RAL 7030
Supply includes	Cable duct with cover
Bar width	5.5 mm 0.22 ″
Slot width	4.5 mm 0.18 ″
Note	Can be shortened for other enclosure sizes.

Features

Dimensions	Width: 50 mm Height: 1,600 mm Depth: 80 mm Width: 1.97 ″ Height: 63 ″ Depth: 3.15 ″
Suitable for	Enclosure type: TS VX SE PC IW Height: ≤ 1,800 mm Enclosure type: TS VX SE PC IW Height: ≤ 70.9 ″
Operating temperature range	60 °C 140 °F
Packaging unit	8 pc(s).
Net weight	8.968 kg
Gross weight	9.44 kg
Customs tariff number	39259020
ETIM 9	EC000012
ECLASS 8.0	27400703
Product description	TS Cable duct for vertical TS section, WHD: 50x1600x80 mm

Approvals

Explanations	Declaration of conformity Declaration of conformity UK