

Rittal – The System.



Faster – better – everywhere.



TS 8801.120

Partial Doors

State: 1/31/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8801.120 - Partial Doors for TS

Door may be optionally hinged on the right or left.



Features

Model No.	TS 8801.120
Product description	Suitable for TS enclosures instead of a door or rear panel. The partial doors can be combined as required. A front trim panel is required at the top and bottom. Door may be optionally hinged on the right or left. In doors without a viewing window (height 600 – 1000 mm), installation of the monitor frame SZ 2305.000 is possible. Standard double-bit lock insert may be exchanged for lock inserts, type F, and for comfort handle in systems 600 mm or more high.
Material	Carbon steel, 2 mm
Color	RAL 7035
Supply includes	Cross member Hinges Lock components Assembly components

Features

Dimensions	Width: 800 mm Height: 200 mm Width: 31.5 " Height: 7.87 "
Protection category IP to IEC 60 529	IP 54 for a completed enclosure
Packaging unit	1 pc(s).
Net weight	3.894
Gross weight	4.094
Customs tariff number	94039910
EAN	4028177250666
ETIM 9	EC000747
ECLASS 8.0	27182204