


Rittal – The System.

Faster – better – everywhere.



TS 8801.560

Partial Doors

State: 4/2/2026 (Source: rittal.com/us-en)



FRIEDHELM LOH GROUP



TS 8801.560 - Partial Doors for TS

Door may be optionally hinged on the right or left.



Features

Model No.	TS 8801.560
Version	Solid
Product description	Suitable for TS enclosures instead of a door or rear panel. The partial doors can be combined as required. A front trim panel is required at the top and bottom. Door may be optionally hinged on the right or left. In doors without a viewing window (height 600 – 1000 mm), installation of the monitor frame SZ 2305.000 is possible. Standard double-bit lock insert may be exchanged for lock inserts, type F, and for comfort handle in systems 600 mm or more high.
Material	Carbon steel, 2 mm
Color	RAL 7035
Supply includes	Cross member Hinges Lock components Assembly components

Features

Dimensions	Width: 600 mm Height: 600 mm Width: 23.6 " Height: 23.6 "
Protection category IP to IEC 60529	IP 54 for a completed enclosure
Packaging unit	1 pc(s).
Net weight	7.413 kg
Gross weight	7.803 kg
Customs tariff number	94039910
ETIM 9	EC000747
ECLASS 8.0	27182204
