

Rittal – The System.

Faster – better – everywhere.



TS 8801.765 Top-mounting module

State: 6/18/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8801.765 - Top-mounting module for TS

As a cable routing compartment for cable infeed from above or for power distribution using busbar systems across bayed enclosures.



Features

Model No.	TS 8801.765
Product description	As a cable routing compartment for cable infeed from above or for power distribution using busbar systems across bayed enclosures. The standard TS roof plate is used to blank off the top of the enclosure.
Material	Carbon steel, 1.5 mm
Surface finish	Spray-finished, textured paint
Color	Similar to RAL 7035
Supply includes	Frame module 2 trim panels front/rear 8 retainers with automatic potential equalization 4 threaded rods with transportation eyebolts
Mounting tip	The top baying cover cannot be fitted
Dimensions	Height: 200 mm Height: 7.87 "
Protection category IP to IEC 60529	IP 55

Features

Suitable for	Enclosure type: TS Width: = 1,200 mm Depth: = 600 mm Enclosure type: TS Width: = 47.2 " Depth: = 23.6 "
Packaging unit	1 pc(s).
Net weight	17.2 kg
Gross weight	18.26 kg
Customs tariff number	94039910
ECLASS 8.0	27182405
Product description	TS Top-mounting module, for TS, for WD: 1200x600 mm

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------
