Rittal – The System.

Faster – better – everywhere.



TS 8808.548

Baying systems TS 8

State: 11/9/2026 (Source: www.rittal.com/us-en)

TS 8808.548 - Baying systems TS 8 Type 3R

Rittal perfected the concept of the industrial modular enclosure with the TS 8 series. These single door, UL Type 3R rated enclosures consist of a frame with door, rear wall, and roof plate. Purchase sidewalls and plinth separately for complete assembly.

Features

Model No.	TS 8808.548
Material	Enclosure frame: Carbon steel, 1.5 mm Roof: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm Rear wall: carbon steel, 1.5 mm Mounting panel: Carbon steel, 3.0 mm
Surface finish	Enclosure frame: powder-coated Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate and base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame with door(s) Roof plate Rear panel, detachable 4 eyebolts Base Plates Mounting plate
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm Width: 31.5 ″ Height: 78.7 ″ Depth: 31.5 ″
Protection category NEMA	NEMA 3R
Packaging unit	1 pc(s).
Net weight	298.995 lb
Gross weight	298.995 lb

© Rittal 2026

Features

Customs tariff number	9403200082

Approvals

Approvals	UL + C-UL (listed)