## Rittal – The System.

Faster – better – everywhere.





TS 8828.548
Baying systems TS 8

State: 11/3/2025 (Source: rittal.com/us-en)



### TS 8828.548 - Baying systems TS 8 Type 3R

Rittal perfected the concept of the industrial modular enclosure with the TS 8 series. These single door, UL Type 3R rated enclosures consist of a frame with door, rear wall, and roof plate. Purchase sidewalls and plinth separately for complete assembly.

#### **Features**

Material	Enclosure frame: Carbon steel, 1.5 mm  Roof: Carbon steel, 1.5 mm  Door: Carbon steel, 2.0 mm  Rear wall: carbon steel, 1.5 mm  Mounting panel: Carbon steel, 3.0 mm
	Door: Carbon steel, 2.0 mm Rear wall: carbon steel, 1.5 mm
	Rear wall: carbon steel, 1.5 mm
	Mounting panel: Carbon steel 3.0 mm
	Wounting parion darbon deed, a.a min
Surface finish	Enclosure frame: powder-coated
	Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint
	Mounting plate and base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame with door(s)
	Roof plate
	Rear panel, detachable
	4 eyebolts
	Base Plates
	Mounting plate
Dimensions	Width: 800 mm
	Height: 2,200 mm
	Depth: 800 mm
	Width: 31.5 "
	Height: 86.6 "
	Depth: 31.5 "
Protection category NEMA	NEMA 3R
Packaging unit	1 pc(s).
Net weight	343.995
Gross weight	343.995

© Rittal 2025 2

### Features

Customs tariff number	7326909099
UPC-Code	85192

# **Approvals**

Approvals	UL + C-UL (listed)
-----------	--------------------

© Rittal 2025 3