Rittal – The System.

Faster – better – everywhere.



GA 9113.210

Cast aluminum housing GA


State: 11/9/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

GA 9113.210 - Cast aluminum housing GA

Spray-finished cast aluminum housing. Protection category IP 66.





Features

Model No.	GA 9113.210
Material	Housing: Cast aluminum Cover: cast aluminum, all-round CR foam rubber round core seal
Surface finish	Textured paint
Color	RAL 7001
Supply includes	Housing with cover Cover screws, captive Screws for attaching support rails Screw for connection of the PE conductor
Dimensions	Width: 260 mm Height: 160 mm Depth: 93 mm Width: 10.2 ″ Height: 6.3 ″ Depth: 3.66 ″
Protection category IP to EN 60 529	IP 66
Protection category NEMA	NEMA 4
IK code	IK08
Base material	Cast aluminum
Packaging unit	1 pc(s).

© Rittal 2026

Features

Net weight	2.2 kg
Gross weight	2.34 kg
Customs tariff number	84879090
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	GA Cast aluminium enclosure, WHD: 260x160x91 mm, Cast aluminum, without mounting plate, with cover

Approvals

Explanations	Declaration of conformity Declaration of conformity UK