Rittal – The System.

Faster – better – everywhere.



SV 9340.010

Busbar Supports

State: 11/7/2026 (Source: www.rittal.com/us-en)

SV 9340.010 - Busbar Supports For Flat Copper Busbars

For flat copper bars up to 800 A.

Features

Model No.	SV 9340.010
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated operating voltage	1000 V, 3~
Note on Model No.:	When 12 x 5/10 mm busbars are used, spacer 9340.090 must also be used
Number of poles	3-pole
Suitable for Model No.	3580000 3581000 3582000 3583000 3584000 3580100 3581100 3585005 3586005
With external attachment	Yes
Center-to-center spacing of busbars	60 mm
Suitable for busbars	15 x 5 - 30 x 10
Packaging unit	4 pc(s).
Net weight	0.76 kg
Gross weight	0.8 kg
Customs tariff number	85369010
ETIM 9	EC001166

© Rittal 2026

Features

ECLASS 8.0	27400607
Product description	SV Busbar support, 3-pole, 60 mm bar centre distance, for busbar WH: 12x5-30x10 mm, (external attachment)

Approvals

Approvals	ABS DNV Lloyds Register
Explanations	Declaration of conformity Declaration of conformity UK