

Rittal – The System.

Faster – better – everywhere.



SV 9340.010

Busbar Supports

State: 2/2/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.010 - Busbar Supports For Flat Copper Busbars

For flat copper bars up to 800 A.

Features

Model No.	SV 9340.010
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated operating voltage	1000 V, 3~
Note on Model No.:	When 12 x 5/10 mm busbars are used, spacer 9340.090 must also be used
Number of poles	3-pole
With external attachment	Yes
Center-to-center spacing of busbars	60 mm
Suitable for busbars	15 x 5 - 30 x 10
Packaging unit	4 pc(s).
Net weight	0.76
Gross weight	0.8
Customs tariff number	85369010
EAN	4028177502338
ETIM 9	EC001166
ECLASS 8.0	27400607

Approvals

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity Declaration of conformity UK