Rittal – The System.

Faster – better – everywhere.



SV 9340.260

OM support

State: 10/31/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9340.260 - OM support without contact system

For mounting of switchgear with external power supply.

Features

Model No.	SV 9340.260
Version	without contact system
Product description	For mounting of switchgear with external power supply.
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
For bar systems with center-to-center spacing	60 mm
Support rail type	Support frame, PinBlock
Number of poles	3-pole
PinBlock	Yes
Dimensions	Width: 45 mm Height: 208 mm Width: 1.77 ″ Height: 8.19 ″
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 ″
Support frame (W x H)	45 mm x 170 mm 1.77 ″ x 6.69 ″
Approvals	UL
Packaging unit	1 pc(s).
Net weight	0.219 kg
Gross weight	0.22 kg
Customs tariff number	85369095
ETIM 9	EC001166

© Rittal 2026

Features

ECLASS 8.0	27400607
Product description	SV OM Support, WH: 45x208 mm, support frame, PinBlock, without contact system

Approvals

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK