Rittal – The System.

Faster – better – everywhere.



SV 9340.270 **OM** support

State: 12/1/2025 (Source: rittal.com/us-en)



SV 9340.270 - OM support without contact system

For mounting of switchgear with external power supply.

Features

Model No.	SV 9340.270
Product description	For mounting of switchgear with external power supply.
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
For bar systems with center-to- center spacing	60 mm
Support rail type	Support frame, 1 x TS 55D-V
Number of poles	3-pole
Support frame support	Yes
Dimensions	Width: 55 mm Height: 272 mm Width: 2.17 " Height: 10.7 "
Support rails Qty/height	1 / 10 mm 0.39 ″
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
Support frame (W x H)	55 mm x 237 mm 2.17 ″ x 9.33 ″
Packaging unit	1 pc(s).
Net weight	0.25
Gross weight	0.258
Customs tariff number	85369095
EAN	4028177502475

© Rittal 2025

Features

ETIM 9	EC001166
ECLASS 8.0	27400607

Approvals

Approvals	ABS
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3