

Rittal – The System.

Faster – better – everywhere.



SV 9340.270

OM support

State: 5/28/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

SV 9340.270 - OM support without contact system

For mounting of switchgear with external power supply.

Features

Model No.	SV 9340.270
Version	without contact system
Product description	For mounting of switchgear with external power supply.
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
For bar systems with center-to-center spacing	60 mm
Support rail type	Support frame, 1 x TS 55D-V
Number of poles	3-pole
Support frame support	Yes
Dimensions	Width: 55 mm Height: 272 mm Width: 2.17 " Height: 10.7 "
Support rails Qty/height	1 / 10 mm 0.39 "
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "
Support frame (W x H)	55 mm x 237 mm 2.17 " x 9.33 "
Approvals	UL
Packaging unit	1 pc(s).
Net weight	0.25 kg
Gross weight	0.258 kg

Features

Customs tariff number	85369095
ETIM 9	EC001166
ECLASS 8.0	27400607
Product description	SV OM Support, WH: 55x272 mm, support frame, support rail TS 55D-V, without contact system

Approvals

Approvals	ABS DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK
