

Rittal – The System.

Faster – better – everywhere.



SV 9340.560 OM adapter

State: 4/28/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.560 - OM adapter with tension spring clamp



Features

Model No.	SV 9340.560
Version	with tension spring clamp
Material	Polyamide Fire protection corresponding to UL 94-V0
Color	Chassis: RAL 7035
Rated current max.	32 A
Rated operating voltage	690 V, 3~
For bar systems with center-to-center spacing	60 mm
Support rail type	Support frame, 1 x TS 45D, 1 x TS 45D-V
Number of poles	3-pole
Support frame support	Yes
Dimensions	Width: 45 mm Height: 272 mm Width: 1.77 " Height: 10.7 "
Connection of round conductors	1.5 - 6 mm ²
Support rails Qty/height	2 / 10 mm 0.39 "
Suitable for busbars	Height: 5, 10 mm Height: 0.2, 0.39 "

Features

Support frame (W x H)	45 mm x 237 mm 1.77 " x 9.33 "
Packaging unit	1 pc(s).
Net weight	0.28 kg
Gross weight	0.293 kg
Copper weight (kg per piece)	0.027
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV OM adaptor, 32 A, 690 V, 3-pole, tension spring clamp 1,5-6 mm ² , WH: 45x272 mm, support frame, support rail TS 45D, TS 45D-V

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity Declaration of conformity UK