

**Rittal – The System.**

Faster – better – everywhere.



# SV 9344.610 Box terminal

State: 5/22/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9344.610 - Box terminal for NH fuse-switch disconnectors

For NH fuse-switch disconnectors size 1 to 3 with screw terminal. For direct connection of round and sector-shaped conductors.



## Features

Model No.	SV 9344.610
Product description	For direct connection of round and sector-shaped conductors as well as laminated copper bars. Suitable for NH fuse-switch disconnectors with screw terminal.
Material	Cast brass
Surface finish	Nickel-plated
Clamping area for laminated copper bars:	Clamping area width: 20 mm Clamping area height: 14 mm Clamping area width: 0.79 " Clamping area height: 0.55 "
Type of connection (electrical)	Box terminal
For size	1
OUT_COL_CROSS_SECTION_SELECTOR_CONDUCTOR	50 - 150 mm <sup>2</sup>
Connection of round conductors	35 - 150 mm <sup>2</sup>
Round conductor cross-section	35 - 150 mm <sup>2</sup>
Packaging unit	3 pc(s).
Net weight	0.171 kg

# Features

---

Gross weight	0.175 kg
Customs tariff number	73182900
ETIM 9	EC001894
ECLASS 8.0	27400609
Product description	SV Box terminal, for NH fuse-switch disconnecter, size 1 (with screw terminal), round conductor connection 35-150 mm <sup>2</sup> , clamping area WH: 20x14 mm