

Rittal – The System.

Faster – better – everywhere.



SV 9344.620 Box terminal

State: 4/17/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.620 - Box terminal for NH fuse-switch disconnectors

For NH fuse-switch disconnectors size 1 to 3 with screw terminal. For direct connection of round and sector-shaped conductors.



Features

| | |
|--|--|
| Model No. | SV 9344.620 |
| Product description | For direct connection of round and sector-shaped conductors as well as laminated copper bars. Suitable for NH fuse-switch disconnectors with screw terminal. |
| Material | Cast brass |
| Surface finish | Nickel-plated |
| Clamping area for laminated copper bars: | Clamping area width: 32 mm Clamping area height: 20 mm Clamping area width: 1.26 " Clamping area height: 0.79 " |
| Type of connection (electrical) | Box terminal |
| For size | 2/3 |
| OUT_COL_CROSS_SECTION_SECTOR_CONDUCTOR | 120 - 300 mm ² |
| Connection of round conductors | 95 - 300 mm ² |
| Round conductor cross-section | 95 - 300 mm ² |
| Packaging unit | 3 pc(s). |
| Net weight | 0.39 kg |

Features

| | |
|-----------------------|--|
| Gross weight | 0.397 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC001894 |
| ECLASS 8.0 | 27400609 |
| Product description | SV Box terminal, for NH fuse-switch disconnecter, size 2/3 (with screw terminal), round conductor connection 95-300 mm ² , clamping area WH: 32x20 mm |