

**Rittal – The System.**

Faster – better – everywhere.



# SV 9344.620 Box terminal

State: 6/19/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9344.620 - Box terminal for NH fuse-switch disconnectors

For NH fuse-switch disconnectors size 1 to 3 with screw terminal. For direct connection of round and sector-shaped conductors.



## Features

Model No.	SV 9344.620
Product description	For direct connection of round and sector-shaped conductors as well as laminated copper bars. Suitable for NH fuse-switch disconnectors with screw terminal.
Material	Cast brass
Surface finish	Nickel-plated
Clamping area for laminated copper bars:	Clamping area width: 32 mm Clamping area height: 20 mm Clamping area width: 1.26 " Clamping area height: 0.79 "
Type of connection (electrical)	Box terminal
For size	2/3
OUT_COL_CROSS_SECTION_SELECTOR_CONDUCTOR	120 - 300 mm <sup>2</sup>
Connection of round conductors	95 - 300 mm <sup>2</sup>
Round conductor cross-section	95 - 300 mm <sup>2</sup>
Packaging unit	3 pc(s).
Net weight	0.39 kg

# Features

Gross weight	0.397 kg
Customs tariff number	39269097
ETIM 9	EC001894
ECLASS 8.0	27400609
Product description	SV Box terminal, for NH fuse-switch disconnecter, size 2/3 (with screw terminal), round conductor connection 95-300 mm <sup>2</sup> , clamping area WH: 32x20 mm