Rittal – The System.

Faster – better – everywhere.



RX 9360.103

RiLineX baying set


State: 11/15/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

RX 9360.103 - RiLineX baying set for basic module

RiLineX baying set, 3-pole, short version, including contact hazard protection cover. Used for baying two boards in a compact arrangement. Ideal for space-saving baying within an enclosure. The set is supplied without busbar connectors (9365003). These are available as accessories.







Features

Model No.	RX 9360.103
Benefits	Scalable system lengths with basic modules Easy mounting Scalable rated currents due to variable busbar cross-sections Tested short circuit resistance up to max. 65 kA Suitable for applications in the alternating current range up to 1,000 V AC and direct current up to 1,500 V DC
Material	Polyamide (PA 6) Fire behavior corresponding to UL 94
Color	RAL 35745
Supply includes	Board end element left and right Board module cover Board module base plate Assembly components
Number of poles	3-pole
Suitable for Model No.	9365.003 9360.110 9360.120 9360.150

© Rittal 2026

Features

Dimensions	Height: 240 mm Depth: 77 mm Height: 9.45 ″ Depth: 3.03 ″
Standards	IEC 61 439-1/-2 UL 508
Protection category IP to IEC 60 529	IP 2XB
Fire load	18.431 MJ/m²
Packaging unit	2 pc(s).
Net weight	1.5 kg
Gross weight	1.752 kg
PCF/VE (cradle-to-gate)	10.18
Customs tariff number	85369010
ETIM 9	EC002270
Product description	RX baying set, 3-pole, for RiLineX basic module, without connector (simple connection)

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration